

Menu Route Map

NOTE

- Red color values indicate the default settings.
- The setting items or setting values with “*” may not be displayed depending on the availability of the optional accessories and other settings.

See the e-Manual for details on settings.

[Setup] Menu

| Control Menu | |
|-----------------------|--|
| Sleep Mode | <div>High (Deep Sleep)</div> <div>Mid (Printer Sleep)</div> |
| Sleep Even if Error | <div>Off</div> <div>On</div> |
| Deep Sleep Eco Prior | <div>Off</div> <div>On</div> |
| Auto Sleep Time | <div>1 min.</div> <div>5 min.</div> <div>10 min.</div> <div>15 min.</div> <div>30 min.</div> <div>60 min.</div> <div>120 min.</div> |
| Sleep When Using USB* | <div>Do Not Allow</div> <div>Allow</div> |
| Timer Settings | <div>Wake Up Timer</div> <div>Off</div> <div>On</div> <div>Wake Up Time</div> <div>12:00 AM to 12:00 PM to 11:59 PM (00:00 to 12:00 to 23:59)</div> <div>Auto Reset Time</div> <div>Off</div> <div>10 sec.</div> <div>20 sec.</div> <div>30 sec.</div> <div>40 sec.</div> <div>50 sec.</div> <div>1 min.</div> <div>2 min.</div> <div>3 min.</div> <div>4 min.</div> <div>5 min.</div> <div>6 min.</div> <div>7 min.</div> <div>8 min.</div> <div>9 min.</div> <div>Sleep Timer</div> <div>Off</div> <div>On</div> <div>Sleep Time</div> <div>12:00 AM to 12:00 PM to 11:59 PM (00:00 to 12:00 to 23:59)</div> <div>Calibration Timer</div> <div>Off</div> <div>On</div> <div>Calibration Time</div> <div>12:00 AM to 12:00 PM to 11:59 PM (00:00 to 12:00 to 23:59)</div> |
| Warning Step | <div>Toner Cart. Warning</div> <div>Continue Printing</div> <div>Stop Printing</div> |
| Auto Skip Error | <div>Off</div> <div>On</div> |
| Language | <div>Čeština</div> <div>Dansk</div> <div>Deutsch</div> <div>English</div> <div>Español</div> <div>Français</div> <div>Italiano</div> <div>Magyar</div> <div>Nederlands</div> <div>Norsk</div> <div>Polski</div> |

Português

Русский

Suomi

Svenska

Türkçe

中文 (简体)

한국어

Alarm

Off

On

Show Warnings

Toner Cart. Warning

Off

On

Drawer Empty

Off

On

E-Mail Trans. Error

Off

On

Date/Time Settings

Date

01/01 2001 to 12/31 2030

12/24 Hour Clock

12 Hour (AM/PM)

24 Hour

Time

12:00:00 AM to 11:59:59 PM
(00:00:00 to 23:59:59)

Daylight Savings

DST Settings: Off, On

Start Date/Time: Month, Week, Day, Time

End Date/Time: Month, Week, Day, Time

Time Zone

GMT-12:00 to GMT-05:00 to GMT+12:00

Main Pwr Quick Start

Off

On

SD Card*

Off

On

Interrupt Print*

Off

On

Sec. Print Del. Time*

1 hr.

2 hr.

3 hr.

6 hr.

12 hr.

24 hr.

Secure Job Log*

Off

On

USB-Connected PC OS

Mac OS

Windows

Other

PDL Selection (PnP)

UFR II

UFR II (V4)

PCL6

PS3

XPS (Direct)

Mng. Settings

Settings Key Lock

Off

On

Sys Manager Settings

Sys Manager Password

RMT-SW

Off

On

| | |
|----------------------|--|
| Adjust Screen | <div>Contrast</div> <div>-3 to 0 to +3</div> <div>Backlight Brightness</div> <div>Off</div> <div>Level 1</div> <div>Level 2</div> <div>Level 3</div> |
| Animated Instruction | <div>Off</div> <div>On</div> |
| Show Toner Gauge | <div>Off</div> <div>On</div> |
| Set. Comp. Notify | <div>Off</div> <div>1 sec.</div> <div>2 sec.</div> <div>3 sec.</div> |
| Scrolling Speed | <div>Slow</div> <div>Normal</div> <div>Fast</div> |

| | |
|-------------------------------------|---|
| Paper Source | <div>Paper Source</div> <div>Auto</div> <div>Multi-Purpose Tray</div> <div>Drawer 1</div> <div>Drawer 2*</div> <div>Drawer 3*</div> <div>Drawer 4*</div> |
| MP Tray Paper Size | <div>A6</div> <div>A5</div> <div>A5R</div> <div>B5</div> <div>A4</div> <div>LTR</div> <div>LGL</div> <div>EXEC</div> <div>Free Size</div> <div>Custom Size</div> <div>Custom Size R</div> <div>Postcard</div> <div>Reply Postcard</div> <div>4on1 Postcard</div> <div>Env. Nagagata3</div> <div>Env. Younaga 3</div> <div>Env. ISO-C5</div> <div>Env. Monarch</div> <div>Env. No.10</div> <div>Env. DL</div> <div>Index Card</div> <div>STMT</div> <div>FLSC</div> <div>16K</div> |
| Drawer N Paper Size (N=1, 2, 3, 4)* | <div>A6</div> <div>A5</div> <div>A5R</div> <div>B5</div> <div>A4</div> <div>LTR</div> <div>LGL*</div> <div>EXEC</div> <div>Free Size</div> <div>Custom Size</div> <div>Custom Size R</div> <div>STMT</div> <div>FLSC*</div> <div>16K</div> |
| Standard Paper Size | <div>A6</div> <div>A5</div> |

B5

A4

LTR

LGL

EXEC

Postcard

Reply Postcard

4on1 Postcard

Env. Nagagata3

Env. Younaga 3

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

MP Tray Priority

Off

On

MP Tray for Mix Ppr.

Off

On

Auto Select Drawer

Do Not Use

Use

Auto Detect Ppr Type

Multi-Purpose Tray

Do Not Use

First Sheet Only

Each Sheet

Drawer 1

Do Not Use

Use

Drawer 2*

Do Not Use

Use

Drawer 3*

Do Not Use

Use

Drawer 4*

Do Not Use

Use

Default Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Heavy 4

Postcard

Envelope

Labels

Rough 1

Rough 2

MP Tray Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Heavy 4

Postcard

Envelope

Rough 1

Rough 2

Mixed Types

Drawer N Paper Type (N=1, 2, 3, 4)*

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Labels

Rough 1

Rough 2

Mixed Types

Manual 2-Sided (MP)

1st Side

2nd Side

2-Sided Printing

Off

On

Network

TCP/IP Settings

IPv4 Settings

IPv4: Off, On

IP Mode: Auto, Manual

Protocol*

Use DHCP: Off, On

Use BOOTP: Off, On

Use RARP: Off, On

Auto IP*: Off, On

IP Address Settings

IP Address: 0.0.0.0 to 255.255.255.255

Subnet Mask: 0.0.0.0 to 255.255.255.255

Gateway Address: 0.0.0.0 to 255.255.255.255

DNS

Primary Address: 0.0.0.0 to 255.255.255.255

Secondary Address: 0.0.0.0 to 255.255.255.255

mDNS Settings*

mDNS: Off, On

mDNS Name*

DHCP Option

Acquire Host Name: Off, On

DNS Dynamic Update: Off, On

IPv6 Settings

IPv6: Off, On

mDNS Settings*

mDNS: Off, On

Use IPv4 Name (mDNS)*: Off, On

mDNS Name*

WINS Resolution

Off

On

FTP

FTP Print: Off, On

Allow Set. via FTP: Off, On

LPD Settings

LPD Print: Off, On

RX Timeout*: 1 to 60 (min.)

RAW Settings

RAW Print: Off, On

RX Timeout*: 1 to 60 (min.)

IPP Print

Off

On

WSD

WSD Print: Off, On

WSD Browsing*: Off, On

Multicast Discovery: Off, On

HTTP

Off

On

Proxy Settings

Proxy: Off, On

Server Address*

Port Number*: 1 to 80 to 65535

Same Domain*: Use Proxy, Do Not Use Proxy

Proxy Authentication*: Off, On

User Name*

Password*

SNTP

Off

On

Discovery Response

Off

On

IPSec

Off

On

Sleep Notif. Set.

Sleep Mode Notif.: Off, On

Port Number*: 1 to 11427 to 65535

Routers to Traverse*: 0 to 3 to 254

Notif. Interval*: 60 to 600 to 65535

Mopria

Off

On

Google Cloud Print

Use Cloud Print

Off

On

Registration Status

SMB*

SMB Server

Off

On

SMB Print*

Off

On

SNMP Settings

SNMPv1 Settings

SNMPv1: Off, On

Dctd. Community Set.

Dctd. Community: Off, Read/Write, Read Only

SNMPv3 Settings

SNMPv3: Off, On

User Settings N (N=1, 2, 3, 4, 5)*

Auth. Password

Encryption Password

Rjct Packet in Sleep

Off

On

Spooler*

Off

On

Receive in Parallel

Off

On

Wait Time at Startup

0 to 300 (sec.)

Remote UI Settings

Remote UI

Off

On

RUI Access Sec. Set.

Off

On

Remote UI Access PIN

TLS*

Off

On

Ethernet Driver

Auto Detect

Off

On

Communication Mode*

Half Duplex

Full Duplex

Ethernet Type*

10 Base-T

100 Base-TX

1000 Base-T

Sleep Mode Priority

Optimal Balance

Exit Speed

Energy Saving

IEEE802.1X

Off

On

Address Filter

Off

On

MAC Address

(Display only)

E-Mail Print Set.

POP3 RX Interval

0 to 90 (min.)

POP3 RX

Off

On

SMTP RX

Off

On

Init. Network Set.

Layout

Number of Copies

1 to 9999

Offset Y

-1.97 to 0.00 to +1.97 (Inches)

(-50.0 to 0.0 to +50.0 (mm))

| | |
|--------------------|---|
| Offset X | -1.97 to 0.00 to +1.97 (Inches) (-50.0 to 0.0 to +50.0 (mm)) |
| Binding Location | Long Edge Short Edge |
| Gutter | -1.97 to 0.00 to +1.97 (Inches) (-50.0 to 0.0 to +50.0 (mm)) |
| Alternative Method | Off On |

Print Quality

Gradation

- High 1
- High 2

Toner Save

- Off
- On

Density: X (X=C, M, Y, K)*

- 8 to 0 to +8

Density X (Fine Adj) (X=C, M, Y, K) *

- High
 - 8 to 0 to +8
- Medium
 - 8 to 0 to +8
- Low
 - 8 to 0 to +8

Color Mode

- Auto (Color/Black)
- Color
- Black

Halftones

- Error Diffusion
 - Off
 - On
- Resolution/Grad.*
 - Text: Resolution, Gradation
 - Graphics: Resolution, Gradation
 - Image: Resolution, Gradation

Gray Compensation

- Text
 - Off
 - On
- Graphics
 - Off
 - On
- Image
 - Off
 - On

CMS

- CMS Selection
 - Printer
 - Host
- CMS/Gamma
 - Text: CMS, Gamma
 - Graphics: CMS, Gamma
 - Image: CMS, Gamma
- RGB Source Profile
 - Text: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4
 - Graphics: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4
 - Image: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4
- Output Profile
 - Text: Normal, Photo
 - Graphics: Normal, Photo
 - Image: Normal, Photo
- Matching Method
 - Text: Perceptual, Saturation, Colorimetric
 - Graphics: Perceptual, Saturation, Colorimetric
 - Image: Perceptual, Saturation, Colorimetric
- Gamma Correction
 - Text: 1.0, 1.4, 1.8, 2.2
 - Graphics: 1.0, 1.4, 1.8, 2.2
 - Image: 1.0, 1.4, 1.8, 2.2

| | |
|--------------------|--|
| Gradation Settings | Gradation - Off Smooth 1 Smooth 2 Graphics* - Off On Image* - Off - On |
| Advanced Smoothing | Advanced Smoothing - Off - Smooth 1 Smooth 2 Graphics* - Off On Text* - Off - On |
| Toner Volume Corr. | Normal Gradation Priority Text Priority |
| Line Control | Resolution Priority Gradation Priority |
| Reduce Quality | Continue Printing Stop Printing |
| Sp. Smoothing Mode | Mode 1 Mode 2 Mode 3 Mode 4 Mode 5 Mode 6 |

Interface

Interface Selection

USB

Off

On

Network

Off

On

USB Adv. Functions

Adv. Func. Settings: Meap Priority, USB Over NW Priority

USB Storage Device

• MEAP Driver: Off, On

Timeout

Timeout

Off

On

Timeout Time*

5 to 15 to 300 (seconds)

Connection Recog.

Off

On

Extended RX Buffer

Off

On

User Maintenance

Adj. Print Position

Offset Y (2-Sided)

└ -0.20 to **0.00** to +0.20 (Inches)
(-5.0 to **0.0** to +5.0 (mm))

Offset X (2-Sided)

└ Multi-Purpose Tray: -0.09 to **0.00** to +0.09 (Inches)
(-2.25 to **0.00** to +2.25 (mm))

└ Drawer 1: -0.09 to **0.00** to +0.09 (Inches)
(-2.25 to **0.00** to +2.25 (mm))

└ Drawer 2*: -0.09 to **0.00** to +0.09 (Inches)
(-2.25 to **0.00** to +2.25 (mm))

└ Drawer 3*: -0.09 to **0.00** to +0.09 (Inches)
(-2.25 to **0.00** to +2.25 (mm))

└ Drawer 4*: -0.09 to **0.00** to +0.09 (Inches)
(-2.25 to **0.00** to +2.25 (mm))

Offset Y (MP Tray)

└ -0.20 to **0.00** to +0.20 (Inches)
(-5.0 to **0.0** to +5.0 (mm))

| | |
|----------------------|---|
| | Offset X (MP Tray) <ul style="list-style-type: none">-0.09 to 0.00 to +0.09 (Inches)(-2.25 to 0.00 to +2.25 (mm)) |
| | Offset Y (Drawer 1 to 4)* <ul style="list-style-type: none">-0.20 to 0.00 to +0.20 (Inches)(-5.0 to 0.0 to +5.0 (mm)) |
| | Offset X (Drawer 1 to 4)* <ul style="list-style-type: none">-0.09 to 0.00 to +0.09 (Inches)(-2.25 to 0.00 to +2.25 (mm)) |
| Recovery Printing | <div>Off</div> <div>On</div> |
| Initialize Counter | <div>Fixing Unit</div> |
| Check Paper Size | <div>Off</div> <div>On</div> |
| Substitute Size | <div>Off</div> <div>On</div> |
| Auto Detect Ppr Type | <div>Mode 1</div> <div>Mode 2</div> <div>Mode 3</div> |
| Short Edge Fd. Prty. | <div>Off</div> <div>On</div> |
| Special Image Mode | <div>Off</div> <div>Level 1</div> <div>Level 2</div> |
| Sp. Transfer Mode | <div>Off</div> <div>On</div> |
| Clr/B&W Switch Mode | <div>Mode 1</div> <div>Mode 2</div> |
| Special Density Mode | <div>Off</div> <div>On</div> |
| SD Card Maintenance* | <div>Format</div> <div>Completely Del. Data</div> |
| Special Print Mode | <div>Curl Correction<ul style="list-style-type: none">OffOn</div> <div>Reduce Waving (Thin)<ul style="list-style-type: none">OffOn</div> <div>Reduce Ppr. Sticking<ul style="list-style-type: none">OffMode 1Mode 2</div> <div>Special Env. Mode<ul style="list-style-type: none">OffOn</div> <div>Corr. White Line<ul style="list-style-type: none">OffOn</div> <div>Reduce Toner Flaking<ul style="list-style-type: none">OffMode 1Mode 2</div> <div>Incr Tail End Fixing<ul style="list-style-type: none">OffOn</div> <div>Reduce Ppr. Slipping<ul style="list-style-type: none">Mode 1Mode 2Mode 3</div> |
| Special Print Adj. C | <div>Off</div> <div>On</div> |
| Adjust Barcode | <div>Normal</div> <div>Narrow</div> |
| Update Firmware | <div>USB</div> <div>Network</div> |
| First Calibration | <div>Color Mismatch Corr.<ul style="list-style-type: none">After JobsImmediately</div> |

Density Control

- After Jobs
- Immediately

Paper Feed Method

- Multi-Purpose Tray
 - Speed Priority
 - Print Side Priority
- Drawer 1 to 4*
 - Speed Priority
 - Print Side Priority

Show Job List

- Off
- On

Low Tnr. Cnsm. Mode

- Off
- On

Import/Export Set.

- IMPORT
- EXPORT

Calibration Freq.

- Standard
- High

Notify to Clean

- Off
- On

Clean. Notif. Timing*

- 1000 to 50000 (pages)

Toner Check Timing

- Default
- Custom

Spec Tnr Chk Timing*

- 1 to 20 to 99 (%)

Print Mode

- Auto Mode Selection
 - Auto Selection
 - PCL
 - PS
 - PDF
 - XPS
- Auto Select
 - PCL
 - Off
 - On
 - PS
 - Off
 - On
 - PDF
 - Off
 - On
 - XPS
 - Off
 - On
- Mode Priority
 - None
 - PCL
 - PS
 - PDF
 - XPS

UFR II

- Paper Save
 - Off
 - On

PCL

- Paper Save
 - Off
 - On
- Orientation
 - Portrait
 - Landscape
- Font Number
 - 0 to 104
- Point Size*
 - 4.00 to 12.00 to 999.75 point
- Pitch*
 - 0.44 to 10.00 to 99.99 cpi
- Form Lines
 - 5 to 60 to 128 lines
- Character Code
 - PC8

ROMAN8

ROMAN9

ISOL1

ISOL2

ISOL5

ISOL6

ISOL9

PC775

PC8DN

PC850

PC852

PC858

PC8TK

PC1004

WINL1

WINL2

WINL5

WINBALT

DESKTOP

PSTEXT

LEGAL

ISO4

ISO6

ISO11

ISO15

ISO17

ISO21

ISO60

ISO69

WIN 30

MCTEXT

PC864

ARABIC8

WINARB

PC866

ISOCYR

WINCYR

PC851

GREEK8

ISOGRK

PC8GRK

WINGRK

PC862

HEBREW7

HEBREW8

ISOHEB

Custom Size

- Do Not Set
- Set

Unit of Measurement*

- Millimeters
- Inches

X Dimension*

- 3.00 to 8.50 in. (76.2 to 215.9 mm)

Y Dimension*

- 5.00 to 14.00 in. (127.0 to 355.6 mm)

Append CR to LF

- Yes
- No

Enlarge A4 Prt Width

- Off
- On

BarDIMM*

- Enable
- Disable

FreeScape*

- Off
- ~
- “
- #
- \$
- /
- \
- ?
- {
- }
- |

Imaging

- Image Orientation
 - Auto
 - Vertical

Horizontal

Zoom

- Off
- Auto

Print Position

- Auto
- Center
- Top Left

TIFF Spooler

- Off
- On

Show Warnings

- Off
- Print
- Panel

Print E-Mail Text

- Off
- On

Limit E-Mail Print*

- Off
- On

Enlarge Print Area

- Off
- On

RGB Source Profile

- sRGB v3.0 (Canon)
- Canon HDTV gamma 1.5
- Canon HDTV gamma 1.8
- Canon HDTV gamma 2.4

CMYK Sim. Profile

- Euro Standard v1.00
- JapanColor(Canon)
- U.S. Web Coated v1.0

Output Profile

- Normal
- Photo

Matching Method

- Perceptual
- Saturation
- Colorimetric

Halftones

- Resolution
- Gradation
- Error Diffusion

Photo Corr (CL Only)*

- Photo Optimizer PRO
 - Off
 - On
- Red-Eye Correction
 - Red-Eye Correction: Off, On
 - Red-Eye Corr. Level*: Weak, Standard, Strong
- Face Brightener
 - Face Brightener: Off, On
 - Face Brightener Lv.*: Weak, Standard, Strong

Grayscale Conversion*

- sRGB
- NTSC
- Uniform RGB

XPS

- Matching Mode
 - ICC Profile
 - Gamma
- ICC Profile Settings
 - RGB Source Profile
 - Text: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4
 - Graphics: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4
 - Image: sRGB v3.0 (Canon), Canon HDTV gamma 1.5, Canon HDTV gamma 1.8, Canon HDTV gamma 2.4
 - Output Profile
 - Text: Normal, Photo
 - Graphics: Normal, Photo
 - Image: Normal, Photo
 - Matching Method
 - Text: Perceptual, Saturation, Colorimetric
 - Graphics: Perceptual, Saturation, Colorimetric
 - Image: Perceptual, Saturation, Colorimetric
- Gamma Settings
 - Gamma Correction

Text: 1.0, **1.4**, 1.8, 2.2

Graphics: 1.0, **1.4**, 1.8, 2.2

Image: 1.0, **1.4**, 1.8, 2.2

Photo Corr (CL Only)

Photo Optimizer PRO

Off

On

Red-Eye Correction

Red-Eye Correction: Off, On

Red-Eye Corr. Level*: Weak, **Standard**, Strong

Face Brightener

Face Brightener: Off, On

Face Brightener Lv.*: Weak, **Standard**, Strong

Halftones

Error Diffusion

Off

On

Resolution/Grad.*

Text: **Resolution**, Gradation

Graphics: Resolution, **Gradation**

Image: Resolution, **Gradation**

Gray Compensation

Text

Off

On

Graphics

Off

On

Image

Off

On

Advanced Smoothing

Advanced Smoothing

Off

Smooth 1

Smooth 2

Graphics*

Off

On

Text*

Off

On

Grayscale Conversion

Text

sRGB

NTSC

Uniform RGB

Graphics

sRGB

NTSC

Uniform RGB

Image

sRGB

NTSC

Uniform RGB

PDF

Fit to Paper Size

Off

On

Enlarge Print Area

Off

On

N on 1

Off

2 on 1

4 on 1

6 on 1

8 on 1

9 on 1

16 on 1

Comment Print

Off

Auto

ICC Profile Settings

RGB Source Profile

sRGB v3.0 (Canon)

Canon HDTV gamma 1.5

Canon HDTV gamma 1.8

Canon HDTV gamma 2.4

None

CMYK Sim. Profile

Euro Standard v1.00

JapanColor(Canon)

U.S. Web Coated v1.0

None

Grayscale Profile

Off

On

Output Profile

Text: PS Normal, PS Photo, PS TR Normal, **PS TR Photo**

Graphics: PS Normal, PS Photo, PS TR Normal, **PS TR Photo**

Image: PS Normal, PS Photo, PS TR Normal, **PS TR Photo**

Matching Method

Perceptual

Saturation

Colorimetric

Pure Black Text

Off

On

Black Overprint*

Off

On

Brightness

85 to **100** to 115 (%)

Halftones

Error Diffusion

Off

On

Resolution/Grad.*

Text: **Resolution**, Gradation

Graphics: Resolution, **Gradation**

Image: Resolution, **Gradation**

Composite Overprint

Off

On

Advanced Smoothing

Advanced Smoothing

Off

Smooth 1

Smooth 2

Graphics*

Off

On

Text*

Off

On

Grayscale Conversion*

sRGB

NTSC

Uniform RGB

PS

Job Timeout

0 to 3600 seconds

Print PS Errors

Off

On

ICC Profile Settings

RGB Source Profile

sRGB v3.0 (Canon)

Canon HDTV gamma 1.5

Canon HDTV gamma 1.8

Canon HDTV gamma 2.4

None

CMYK Sim. Profile

Euro Standard v1.00

JapanColor(Canon)

U.S. Web Coated v1.0

None

Grayscale Profile

Off

On

Output Profile

Text: PS Normal, PS Photo, PS TR Normal, **PS TR Photo**

Graphics: PS Normal, PS Photo, PS TR Normal, **PS TR Photo**

Image: PS Normal, PS Photo, PS TR Normal, **PS TR Photo**

Matching Method

Perceptual

Saturation

Colorimetric

Pure Black Text

Off

On

Black Overprint*

Off

On

Brightness

85 to **100** to 115 (%)

Halftones

Error Diffusion

Off

On

Resolution/Grad.*

Text: **Resolution**, Gradation

Graphics: Resolution, **Gradation**

Image: Resolution, **Gradation**

Composite Overprint

Off

On

Advanced Smoothing

Advanced Smoothing

Off

Smooth 1

Smooth 2

Graphics*

Off

On

Text*

Off

On

Grayscale Conversion*

sRGB

NTSC

Uniform RGB

MEAP Settings

Select Def. Screen

Print Screen

MEAP

Check Counter

101: Total 1

(Display only)

108: Total (B&W 1)

(Display only)

322:Print(Full+1C/S)

(Display only)

Initialize Menu

[Utility] Menu

Check Counter

101: Total 1

(Display only)

108: Total (B&W 1)

(Display only)

322:Print(Full+1C/S)

(Display only)

Configuration Page

Network Status Print

ConsmbL. Status Prt.

IPSec Policy List

Calibration

Color Mismatch Corr.

Density Control

Full Calibration

PCL Utility

Font List

PS Utility

Configuration Page

Font List

Cleaning

A4

LTR

Control Condensation

E-Mail Print Utility

Received E-Mail

E-Mail RX Log List

Printing Pos. Print

Page Count List

Counter Report

Print MEAP Sys. Info

Serial Number

(Display only)

Consumables Info.

Paper Information

Multi-Purpose Tray: (Display only)

Drawer 1: (Display only)

Drawer 2*: (Display only)

Drawer 3*: (Display only)

Drawer 4*: (Display only)

Toner Cart. Model

Cyan: (Display only)

Magenta: (Display only)

Yellow: (Display only)

Black: (Display only)

Remaining Toner

Cyan: (Display only)

Magenta: (Display only)

Yellow: (Display only)

Black: (Display only)

Waste Toner cntnr.

(Display only)

Waste Toner Status

(Display only)

[Job] Menu

Encrypted Print*

Secured Print*

Stored Job List*

Stored Job Print*

Job Print Log*

Stored Job Print Log*

Report Print Log*

E-Mail Print Log*

[Reset] Menu

Soft Reset (Hard Reset)

Form Feed

Shut Down

[Select Feeder] Menu

Paper Source

Auto

Multi-Purpose Tray

Drawer 1

Drawer 2*

Drawer 3*

Drawer 4*

MP Tray Paper Size

A6

A5

A5R

B5

A4

LTR

LGL

EXEC

Free Size

Custom Size

Custom Size R

Postcard

Reply Postcard

4on1 Postcard

Env. Nagagata3

Env. Younaga 3

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

Drawer N Paper Size (N=1, 2, 3, 4)*

A6

A5

A5R

B5

A4

LTR

LGL*

EXEC

Free Size

Custom Size

Custom Size R

STMT

FLSC*

16K

Standard Paper Size

A6

A5

B5

A4

LTR

LGL

EXEC

Postcard

Reply Postcard

4on1 Postcard

Env. Nagagata3

Env. Younaga 3

Env. ISO-C5

Env. Monarch

Env. No.10

Env. DL

Index Card

STMT

FLSC

16K

MP Tray Priority

Off

On

MP Tray for Mix Ppr.

Off

On

Auto Select Drawer

Do Not Use

Use

Auto Detect Ppr Type

Multi-Purpose Tray

Do Not Use

First Sheet Only

Each Sheet

Drawer 1

Do Not Use

Use

Drawer 2*

Do Not Use

Use

Drawer 3*

Do Not Use

Use

Drawer 4*

Do Not Use

Use

Default Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Heavy 4

Postcard

Envelope

Labels

Rough 1

Rough 2

MP Tray Paper Type

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Heavy 4

Postcard

Envelope

Rough 1

Rough 2

Mixed Types

Drawer N Paper Type (N=1, 2, 3, 4)*

Plain

Plain L

Plain L2

Heavy 1

Heavy 2

Heavy 3

Labels

Rough 1

Rough 2

Mixed Types

Manual 2-Sided (MP)

1st Side

2nd Side

2-Sided Printing

Off

On