






Menu Route Map




Settings marked with an asterisk (*) cannot be imported or exported via the Remote UI.



Settings marked with an asterisk (*) are only available when the optional Cassette Feeding Unit is attached.



Settings marked with an asterisk (*) are only available when the optional Cassette Feeding Unit is attached.



Settings marked with an asterisk (*) cannot be imported or exported via the Remote UI.

Menu Route Map

Scan Settings

USB Memory Settings

- Change Default Settings
 - Scan Size
 - A4, A5, B5, **LTR**, LGL, STMT
 - Color Mode
 - Color**, Black & White
 - File Format
 - PDF (Compact), **PDF**, PDF (Compact/OCR), PDF (OCR), JPEG, TIFF, Set PDF Details*
 - Encryption
 - None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures
 - None**, Top Left
 - Density
 - 9 Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, **Text/Photo**, Photo
 - 2-Sided Original
 - Off**, Book Type, Calendar Type
 - Sharpness
 - 7 Levels
 - Data Size
 - Small: Memory Priority, **Standard**, Large: Image Quality Priority
- Initialize Default Settings

E-Mail Settings

- Change Default Settings
 - Scan Size
 - A4, A5, B5, **LTR**, LGL, STMT
 - Color Mode
 - Color**, Black & White
 - File Format
 - PDF (Compact), **PDF**, PDF (Compact/OCR), PDF (OCR), JPEG, TIFF, Set PDF Details*
 - PDF
 - Encryption Level: **None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures : **None**, Top Left
 - Divide into Pages: **Off**, On
 - PDF(Compact)
 - Encryption Level: **None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures : **None**, Top Left
 - Divide into Pages: **Off**, On
 - PDF (Compact/OCR)
 - Encryption Level: **None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures : **None**, Top Left
 - Divide into Pages: **Off**, On
 - PDF(OCR)
 - Encryption Level: **None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures : **None**, Top Left
 - Divide into Pages: **Off**, On
 - TIFF
 - Divide into Pages: **Off**, On
 - Density
 - 9 Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, **Text/Photo**, Photo
 - 2-Sided Original
 - Off**, Book Type, Calendar Type
 - Sharpness
 - 7 Levels
 - Data Size
 - Small: Memory Priority, **Standard**, Large: Image Quality Priority
 - Subject/Message
 - Subject, Message
 - Reply To
 - None**, Specify from Address Book
 - Priority
 - Low, **Standard**, High
 - Register Unit Name (E-Mail)
 - Initialize Default Settings

File Settings

- Change Default Settings
 - Scan Size
 - A4, A5, B5, **LTR**, LGL, STMT
 - Color Mode
 - Color**, Black & White
 - File Format
 - PDF (Compact), **PDF**, PDF (Compact/OCR), PDF (OCR), JPEG, TIFF, Set PDF Details*
 - PDF
 - Encryption Level: **None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures : **None**, Top Left
 - Divide into Pages: **Off**, On
 - PDF(Compact)
 - Encryption Level: **None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures : **None**, Top Left
 - Divide into Pages: **Off**, On
 - PDF (Compact/OCR)
 - Encryption Level: **None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures : **None**, Top Left
 - Divide into Pages: **Off**, On
 - PDF(OCR)
 - Encryption Level: **None**, Acrobat 7.0 or Later/128-bit AES, Acrobat 9.0 or Equivalent/256-bit AES, Acrobat 10.0 or Equivalent/256-bit AES
 - Digital Signatures : **None**, Top Left
 - Divide into Pages: **Off**, On
 - TIFF
 - Divide into Pages: **Off**, On
 - Density
 - 9 Levels
 - Original Orientation
 - Portrait, Landscape
 - Original Type
 - Text, **Text/Photo**, Photo
 - 2-Sided Original
 - Off**, Book Type, Calendar Type
 - Sharpness
 - 7 Levels
 - Data Size
 - Small: Memory Priority, **Standard**, Large: Image Quality Priority
 - Initialize Default Settings

Output File Image Settings

- YCbCr TX Gamma Value
 - Gamma 1.0, Gamma 1.4, **Gamma 1.8**, Gamma 2.2
- PDF (Compact) Image Quality Level
 - Image Level in Text/Photo Mode or Photo Mode
 - Data Size Priority, **Normal**, Image Quality Priority
 - Image Level in Text Mode
 - Data Size Priority, **Normal**, Image Quality Priority

OCR (Text Searchable) Settings

- Smart Scan
 - Off, **On**

256-bit AES Settings for Encrypted PDF*

- Acrobat 9.0 or Equivalent, **Acrobat 10.0 or Equivalent**

Settings marked with an asterisk (*) are enabled only when an optional Send PDF Security Feature Set is registered.

Memory Media Print Settings

Change Default Settings

- Number of Copies
 - 1** to 99
- Color Mode
 - Color**, Black & White
- Paper
 - Multi-Purpose Tray, **Drawer 1**, Drawer 2*, Drawer 3*, Drawer 4*
- N on 1
 - Off**, 2 on 1, 4 on 1
- 2-Sided
 - Off**, Book Type, Calendar Type
- Set JPEG/TIFF Details
 - Print Date
 - Off**, On
 - Print File Name
 - Off**, On
 - Original Type
 - Photo Priority**, Text Priority
 - Brightness
 - 5 Levels
 - Halftones
 - Gradation, **Error Diffusion**
- Set PDF Details
 - Brightness
 - 7 Levels
 - Enlarge/Reduce to Fit Ppr. Size
 - Off**, On
 - Enlarge Print Area
 - Off**, On
 - Print Comments
 - Off, **Auto**
 - Password to Open Document
 - Other
 - Halftones
 - Error Diffusion: **Off**, On
 - Pure Black Text
 - Off, **On**
 - Black Overprint
 - Off, **On**
 - RGB Source Profile
 - sRGB**, Gamma 1.5, Gamma 1.8, Gamma 2.4, None
 - CMYK Simulation Profile
 - JapanColor(Canon), U.S. Web Coated v1.00(Canon), Euro Standard v1.00(Canon), **None**
 - Use Grayscale Profile
 - Off**, On
 - Output Profile
 - Normal, Photo, **TR Normal**, TR Photo
 - Matching Method
 - Perceptual**, Saturation, Colorimetric
 - RGB Pure Black Process
 - Off, **On**
 - CMYK Pure Black Process
 - Off, **On**
 - Composite Overprint
 - Off**, On
 - Advanced Smoothing
 - Advanced Smoothing
 - Off, **Smooth 1**, Smooth 2
 - Apply to Graphics
 - Off, **On**
 - Apply to Text
 - Off, **On**
 - Grayscale Conversion
 - sRGB, **NTSC**, Uniform RGB
 - Print Quality

Default Display Settings

- Details**, Images

File Sort Default Settings

- Name (Ascending)**, Name (Descending), Date/Time (Ascending), Date/Time (Descending)

File Name Display Format

- Short File Name, **Long File Name**

Initialize Default Settings

Settings marked with an asterisk (*) are only available when the optional Cassette Feeding Unit is attached.

Menu Route Map

Printer Settings	
Copies	1 to 99 (Copies)
2-Sided Printing	Off, On
Default Paper	Default Paper Size <ul style="list-style-type: none">LTR, LGL, STMT, EXEC, FOOLSCAP, OFICIO, No. 10 (COM10), Monarch, DL, ISO-C5, Government-LTR, Government-LGL, AUS-FOOLSCAP, Brazil-OFICIO, Mexico-OFICIO, Korean-LGL, F4A, A4, A5, B5, Nagagata 3, Yougatanaga 3, Postcard, Reply Postcard, 4 on 1 Postcard, Custom Default Paper Type <ul style="list-style-type: none">Plain 1 (18 lb Bond-20 lb Bond)/(64-75 g/m²), Plain 2 (21 lb Bond-24 lb Bond)/(76-90 g/m²), Plain 3 (25 lb Bond-27 lb Bond)/(91-105 g/m²), Recycled 1 (18 lb Bond-20 lb Bond)/(64-75 g/m²), Recycled 2 (21 lb Bond-24 lb Bond)/(76-90 g/m²), Recycled 3 (25 lb Bond-27 lb Bond)/(91-105 g/m²), Color, Heavy 1 (29 lb Bond-34 lb Bond)/(106-128 g/m²), Heavy 2 (35 lb Bond-60 lb Cover)/(129-163 g/m²), Heavy 3 (61 lb Cover-81 lb Cover)/(164-220 g/m²), Postcard, Envelope, Thin (16 lb Bond)/(60-63 g/m²), Transparency, Labels, Bond (23 lb Bond)/(90 g/m²)
Paper Size Override	Off, On
Print Quality	Density <ul style="list-style-type: none">Yellow<ul style="list-style-type: none">17 LevelsMagenta<ul style="list-style-type: none">17 LevelsCyan<ul style="list-style-type: none">17 LevelsBlack<ul style="list-style-type: none">17 Levels Density (Fine Adjust) <ul style="list-style-type: none">Yellow<ul style="list-style-type: none">High: 17 LevelsMedium: 17 LevelsLow: 17 LevelsMagenta<ul style="list-style-type: none">High: 17 LevelsMedium: 17 LevelsLow: 17 LevelsCyan<ul style="list-style-type: none">High: 17 LevelsMedium: 17 LevelsLow: 17 LevelsBlack<ul style="list-style-type: none">High: 17 LevelsMedium: 17 LevelsLow: 17 Levels Toner Save <ul style="list-style-type: none">Off, On Gradation <ul style="list-style-type: none">High 1, High 2 Special Smoothing Mode <ul style="list-style-type: none">Mode 1, Mode 2, Mode 3, Mode 4, Mode 5, Mode 6 Toner Volume Correction <ul style="list-style-type: none">Normal, Gradation Priority, Text Priority Line Control <ul style="list-style-type: none">Resolution Priority, Gradation Priority
Layout	Binding Location <ul style="list-style-type: none">Long Edge, Short Edge Gutter <ul style="list-style-type: none">-1.90 to ±0 to +1.90 (inches) or -50.0 to ±0 to +50.0 (mm) Offset Short Edge (Front) <ul style="list-style-type: none">-2.00 to ±0 to +2.00 (inches) or -50.0 to ±0 to +50.0 (mm) Offset Long Edge (Front) <ul style="list-style-type: none">-2.00 to ±0 to +2.00 (inches) or -50.0 to ±0 to +50.0 (mm) Offset Short Edge (Back) <ul style="list-style-type: none">-2.00 to ±0 to +2.00 (inches) or -50.0 to ±0 to +50.0 (mm) Offset Long Edge (Back) <ul style="list-style-type: none">-2.00 to ±0 to +2.00 (inches) or -50.0 to ±0 to +50.0 (mm)
Auto Error Skip	Off, On
Timeout	5 to 15 to 300 (sec.)
Personality	Auto, PS, PCL
Color Mode	Auto (Color/B&W), Color, Black and White
Gradation Settings	Gradation <ul style="list-style-type: none">Off, Smooth 1, Smooth 2 Apply to Graphics <ul style="list-style-type: none">Off, On Apply to Images <ul style="list-style-type: none">Off, On
Compressed Image Output	Output, Display Error

UFR II	
Halftones	Error Diffusion <ul style="list-style-type: none">Off, On Resolution/Gradation <ul style="list-style-type: none">Text<ul style="list-style-type: none">Resolution, GradationGraphics<ul style="list-style-type: none">Resolution, GradationImage<ul style="list-style-type: none">Resolution, Gradation
RGB Source Profile	Text <ul style="list-style-type: none">sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4 Graphics <ul style="list-style-type: none">sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4 Image <ul style="list-style-type: none">sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4
Output Profile	Text <ul style="list-style-type: none">Normal, Photo Graphics <ul style="list-style-type: none">Normal, Photo Image <ul style="list-style-type: none">Normal, Photo
Matching Method	Text <ul style="list-style-type: none">Perceptual, Saturation, Colorimetric Graphics <ul style="list-style-type: none">Perceptual, Saturation, Colorimetric Image <ul style="list-style-type: none">Perceptual, Saturation, Colorimetric
Gray Compensation	Text <ul style="list-style-type: none">Off, On Graphics <ul style="list-style-type: none">Off, On Image <ul style="list-style-type: none">Off, On
CMS (Matching) Selection	Printer, Host
CMS (Matching)/Gamma	Text <ul style="list-style-type: none">Gamma, CMS Graphics <ul style="list-style-type: none">Gamma, CMS Image <ul style="list-style-type: none">Gamma, CMS
Gamma Correction	Text <ul style="list-style-type: none">1.0, 1.4, 1.8, 2.2 Graphics <ul style="list-style-type: none">1.0, 1.4, 1.8, 2.2 Image <ul style="list-style-type: none">1.0, 1.4, 1.8, 2.2
Paper Save	Off, On
Advanced Smoothing	Advanced Smoothing <ul style="list-style-type: none">Off, Smooth 1, Smooth 2 Apply to Graphics <ul style="list-style-type: none">Off, On Apply to Text <ul style="list-style-type: none">Off, On
PCL	
Paper Save	Off, On
Orientation	Portrait, Landscape
Font Number	0 to 104
Point Size	4.00 to 12.00 to 999.75 (point)
Pitch	0.44 to 10.00 to 99.99 (dpi)
Form Lines	5 to 60 to 128 (lines)
Character Code	ARABIC8, DESKTOP, GREEK8, HEBREW7, HEBREW8, ISO4, ISO6, ISO11, ISO15, ISO17, ISO21, ISO60, ISO69, ISOCYR, ISOGRK, ISOHEB, ISOL1, ISOL2, ISOL5, ISOL6, LEGAL, MATH8, MCTEXT, MSPUBL, PC775, PC8, PC850, PC852, PC862, PC864, PC866, PC8DN, PC8GRK, PC8TK, PC1004, PIFONT, PSMATH, PSTEXT, ROMAN8, VNINTL, VNMath, VNUS, WIN30, WINARB, WINBALT, WINCYR, WINGRK, WINL1, WINL2, WINL5
Custom Paper	Off, On
Unit of Measure	Millimeters, Inches
X dimension	3 15/16 to 8 1/2 (inches) or 99 to 216 (mm)
Y dimension	5 7/8 to 13 15/16 (inches) or 148 to 355 (mm)
Append CR to LF	Yes, No
Enlarge A4 Print Width	Off, On
Halftones	Error Diffusion <ul style="list-style-type: none">Off, On Resolution/Gradation <ul style="list-style-type: none">Text<ul style="list-style-type: none">Resolution, GradationGraphics<ul style="list-style-type: none">Resolution, GradationImage<ul style="list-style-type: none">Resolution, Gradation
RGB Source Profile	Text <ul style="list-style-type: none">sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4 Graphics <ul style="list-style-type: none">sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4 Image <ul style="list-style-type: none">sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4

Output Profile	Text <ul style="list-style-type: none">Normal, Photo Graphics <ul style="list-style-type: none">Normal, Photo Image <ul style="list-style-type: none">Normal, Photo
Matching Method	Text <ul style="list-style-type: none">Perceptual, Saturation, Colorimetric Graphics <ul style="list-style-type: none">Perceptual, Saturation, Colorimetric Image <ul style="list-style-type: none">Perceptual, Saturation, Colorimetric
Gray Compensation	Text <ul style="list-style-type: none">Off, On Graphics <ul style="list-style-type: none">Off, On Image <ul style="list-style-type: none">Off, On
CMS (Matching) Selection	Printer, Host
CMS (Matching)/Gamma	Text <ul style="list-style-type: none">Gamma, CMS Graphics <ul style="list-style-type: none">Gamma, CMS Image <ul style="list-style-type: none">Gamma, CMS
Gamma Correction	Text <ul style="list-style-type: none">1.0, 1.4, 1.8, 2.2 Graphics <ul style="list-style-type: none">1.0, 1.4, 1.8, 2.2 Image <ul style="list-style-type: none">1.0, 1.4, 1.8, 2.2
Advanced Smoothing	Advanced Smoothing <ul style="list-style-type: none">Off, Smooth 1, Smooth 2 Apply to Graphics <ul style="list-style-type: none">Off, On Apply to Text <ul style="list-style-type: none">Off, On
BarDIMM*	Enable, Disable
PS	
Job Timeout	0 to 3600 (sec.)
Print PS Errors	Off, On
Pure Black Text	Off, On
Black Overprint	Off, On
RGB Source Profile	sRGB, Gamma 1.5, Gamma 1.8, Gamma 2.4, None
CMYK Simulation Profile	JapanColor(Canon), U.S. Web Coated v1.00(Canon), Euro Standard v1.00(Canon), None
Use Grayscale Profile	Off, On
Output Profile	Normal, Photo, TR Normal, TR Photo
Matching Method	Perceptual, Saturation, Colorimetric
RGB Pure Black Process	Off, On
CMYK Pure Black Process	Off, On
Halftones	Error Diffusion <ul style="list-style-type: none">Off, On Resolution/Gradation <ul style="list-style-type: none">Text<ul style="list-style-type: none">Resolution, GradationGraphics<ul style="list-style-type: none">Resolution, GradationImage<ul style="list-style-type: none">Resolution, Gradation
Brightness	85 to 100 to 115 (%)
Composite Overprint	Off, On
Advanced Smoothing	Advanced Smoothing <ul style="list-style-type: none">Off, Smooth 1, Smooth 2 Apply to Graphics <ul style="list-style-type: none">Off, On Apply to Text <ul style="list-style-type: none">Off, On
Grayscale Conversion	sRGB, NTSC, Uniform RGB

Settings marked with an asterisk (*) are only available when an optional Print Kit is registered.

Adjustment/Maintenance	
Auto Adjust Gradation	Full Adjust (Plain Paper 1/2), Full Adjust (Plain Paper 3), Full Adjust (Heavy Paper), Quick Adjust, Adjust Copy Image
Auto Correction Settings	Auto Adjust Image Regularly <ul style="list-style-type: none">Off, On
Correct Print Color Mismatch	
Black Text Processing for Color	Feeder <ul style="list-style-type: none">7 Levels Platen Glass <ul style="list-style-type: none">7 Levels
Special Processing	Special Paper Processing <ul style="list-style-type: none">Envelope Cling Prevention<ul style="list-style-type: none">Off, OnEnvelope Fixing Speed Settings<ul style="list-style-type: none">-20 to 20 Adjust Toner Volume Used for Color Printing <ul style="list-style-type: none">Off, Level 1, Level 2 Heavy Paper Curl Reduction Mode <ul style="list-style-type: none">Off, On Fill Area Image Adjustment Mode <ul style="list-style-type: none">Mode 1, Mode 2, Mode 3
Clean Fixing Assembly	
Clean Device	
Special Cleaning	Adjust Level <ul style="list-style-type: none">Level 1, Level 2, Level 3 Start
Clean Feeder	
Remove Streaks from Original Scanning Area	Off, On
Initialize After Replacing Parts	Secondary Transfer Outer Roller, Fixing Assembly, ADF Pickup Roller and ADF Separation Pad, ITB

Menu Route Map

System Management Settings	
Network Settings	->Network Settings
System Manager Information Settings	
System Manager ID and PIN	System Manager ID
	System Manager PIN
	System Manager Name
Device Information Settings	
Device Name	
Location	
Department ID Management On/Off	
	Off, On
Security Settings	
Use SSL	Off, On
Use IPsec	Off, On
IPv4 Address Filter	
Outbound Filter	Off, On
Inbound Filter	Off, On
IPv6 Address Filter	
Outbound Filter	Off, On
Inbound Filter	Off, On
MAC Address Filter	
Outbound Filter	Off, On
Inbound Filter	Off, On
Communication Management Settings	
Fax Settings	
TX Start Speed	33600 bps, 14400 bps, 9600 bps, 7200 bps, 4800 bps, 2400 bps
RX Start Speed	33600 bps, 14400 bps, 9600 bps, 7200 bps, 4800 bps, 2400 bps
Archive TX Document*	Off, On
Memory Lock Settings	
Off, On	
Memory Lock PIN	
Report Print	Off, On
Memory Lock Time	Off, On
Memory Lock Start Time	
Memory Lock End Time	
Select Country/Region*	
United States (US), Canada (CA), Brazil (BR), Mexico (MX), Other	
Forwarding Settings*	
	Off, On
Store/Print When Forwarding	
Print Images	Off, On, Only When Error Occurs
Store Images in Memory	Off, Only When Error Occurs
Remote UI Settings*	
Use Remote UI	Off, On
Restrict TX Function	
Address Book PIN	
Restrict New Destinations	Off, On
Allow Fax Driver TX	Off, On
Restrict Resending from Log	Off, On
Confirm Entered Fax Number	Off, On
Coded Dial TX Confirmation	Off, On
Restrict Sequential Broadcast	Off, Confirm Sequential Broadcast, Reject Sequential Broadcast

Display Job Log	Off, On
Use as USB Device	Off, On
Store to USB Memory	Off, On
Memory Media Print On/Off	Off, On
Enable Product Extended Survey Program	Off, On
Enable Canon Mobile Scanning	Off, On
Google Cloud Print Settings*	
Enable Google Cloud Print	Off, On
Google Cloud Print Registration Status	
Import/Export of Settings*	
	Import, Export
Secure Print Settings	
Off, On(Secure Print Deletion Time)	10 to 30 to 240 (min.)
PDL Selection (Plug and Play)	
Network	
Fax, UFR II, UFR II (XPS)	
USB	UFR II, UFR II (XPS)
Register License*	
Update Firmware*	
Via PC, Via Internet	
Initialize Key and Certificate*	
Initialize Address Book*	
Initialize Menu*	
Preferences	
Timer Settings	
Common Settings	
Copy Settings	
Fax Settings	
Scan Settings	
Memory Media Print Settings	
Printer Settings	
System Management Settings	
Network Settings	
System Manager Information Settings	
Device Information Settings	
Department ID Management On/Off	
Security/Remote UI Settings	
Communication Management Settings	
Forwarding Settings	
Store/Print When Forwarding	
Restrict TX Function	
Register LDAP Server	
Display Job Log	
Use as USB Device	
Store to USB Memory	
Memory Media Print On/Off	
Enable Product Extended Survey Program	
Google Cloud Print Settings	
Enable Canon Mobile Scanning	
Secure Print Settings	
PDL Selection (Plug and Play)	
Initialize All	
Initialize All	

Settings marked with an asterisk (*) cannot be imported or exported via the Remote UI.