

Menu Route Map

Paper Settings

- Multi-Purpose Tray
- Drawer 1
- Drawer 2*
- Register Custom Paper
- Select Frequently Used Paper Sizes

Settings marked with an asterisk (*) are only available when the optional paper feeder (drawer 2) is attached.

Network Settings

- Select Wired/Wireless LAN
 - Wired LAN, Wireless LAN
- Wireless LAN Settings
 - WPS Push Button Mode
 - WPS PIN Code Mode
 - SSID Settings
 - Select Access Point
 - Enter Manually
 - Security Settings
 - None
 - WEP
 - Open System, Shared Key
 - WPA/WPA2-PSK
 - Auto, AES-CCMP
 - Power Save Mode
 - Off, On
 - Connection Information
 - MAC Address
 - Wireless LAN Status
 - Latest Error Information
 - Channel
 - SSID Settings
 - Security Settings
 - Power Save Mode
- Enable Direct Connection
 - Off, On

TCP/IP Settings

- IPV4 Settings
 - IP Address Settings
 - Auto Acquire
 - Select Protocol
 - Off, DHCP
 - Auto IP
 - Off, On
 - Manually Acquire
 - IP Address: 0.0.0.0
 - Subnet Mask: 0.0.0.0
 - Gateway Address: 0.0.0.0
 - Check Settings
 - Auto Acquire
 - IP Address
 - Subnet Mask
 - Gateway Address
 - PING Command
 - DNS Settings
 - DNS Server Settings
 - Primary DNS Server: 0.0.0.0
 - Secondary DNS Server: 0.0.0.0
 - DNS Host Name/Domain Name Settings
 - Host Name
 - Domain Name
 - DNS Dynamic Update Settings
 - Off, On
 - 0 to 24 to 48 (hr.)
 - mDNS Settings
 - Off, On(mDNS Name)
 - DHCP Option Settings
 - Acquire Host Name
 - Off, On
 - DNS Dynamic Update
 - Off, On
 - Acquire DNS Server Address
 - Off, On
 - Acquire Domain Name
 - Off, On
 - Acquire WINS Server Address
 - Off, On
 - IPV6 Settings
 - Use IPv6
 - Off, On, Check Settings
 - Link-Local Address
 - Prefix Length
 - Stateless Address Settings
 - Off, On, Check Settings
 - Stateless Address
 - Prefix Length
 - Use DHCPv6
 - Off, On, Check Settings
 - Stateful Address
 - Prefix Length
 - DNS Settings
 - DNS Host Name/Domain Name Settings (Use IPv4 Host/Domain)
 - Off, On
 - Host Name
 - Domain Name
 - DNS Dynamic Update Settings
 - Off, On
 - Register Manual Address
 - Off, On
 - Register Stateful Address
 - Off, On
 - Register Stateless Address
 - Off, On
 - DNS Dynamic Update Interval
 - 0 to 24 to 48 (hr.)
 - mDNS Settings
 - Off, On(Use Same mDNS Name as IPv4)
 - Off(mDNS Name), On
 - DHCP Option Settings
 - Acquire DNS Server Address
 - Off, On
 - Acquire Domain Name
 - Off, On
 - WINS Settings
 - WINS Resolution
 - Off, On(WINS Server Address: 0.0.0.0)
 - LPD Settings
 - LPD Print Settings
 - Off, On
 - RX Timeout
 - 1 to 5 to 60 (min.)
 - RAW Settings
 - RAW Print Settings
 - Off, On
 - RX Timeout
 - 1 to 5 to 60 (min.)
 - WSD Settings
 - WSD Print Settings
 - Use WSD Print
 - Off, On
 - Use WSD Browsing
 - Off, On
 - Use Multicast Discovery
 - Off, On
 - Use HTTP
 - Off, On
 - IPP Print Settings
 - Use IPP Printing
 - Off, On
 - Use TLS
 - Off, On

Port Number Settings

- LPD
 - 1 to 515 to 65535
- RAW
 - 1 to 9100 to 65535
- WSD Multicast Discovery
 - 1 to 3702 to 65535
- HTTP
 - 1 to 80 to 65535
- Multicast Discovery
 - 1 to 427 to 65535
- SNMP
 - 1 to 161 to 65535
- MTU Size
 - 1300, 1400, 1500

SNMP Settings

- SNMPV1 Settings
 - Off, On
- SNMPV3 Settings
 - Off, On
- Acquire Printer Management Information from Host
 - Off, On

Dedicated Port Settings

- Off, On

Waiting Time for Connection at Startup

- 0 to 300 (sec.)

Ethernet Driver Settings

- MAC Address
- Auto Detect
 - Off, On
 - Communication Mode
 - Half Duplex, Full Duplex
 - Ethernet Type
 - 10BASE-T, 100BASE-TX, 1000BASE-T

IEEE 802.1X Settings

- Off, On

Device Settings Management On/Off

- Off, On

Initialize Network Settings

Preferences

Volume Settings

- Entry Tone
 - Off, On
- Invalid Entry Tone
 - Off, On
- Restock Supplies Tone
 - Off, On
- Job Done Tone
 - Off, On
- Energy Saver Alert
 - Off, On

Display Settings

- Default Screen after Startup/Restoration
 - Home, Memory Media Print
- Brightness
 - Five Levels
- Invert Screen Colors
 - Off, On
- Millimeter/Inch Entry Switch
 - Millimeter, Inch
- Gram/Pound Switch
 - Gram, Pound
- Message Display Time
 - 1 to 2 to 5 (sec.)
- Scrolling Speed
 - Slow, Standard, Fast
- Cursor Movement Type
 - Auto, Manual
- Language
 - English, Japanese, French, Spanish, German, Italian, Portuguese, Chinese (Simplified), Chinese (Traditional), Korean
- Remote UI Language
 - English, Japanese, French, Spanish, German, Italian, Portuguese, Chinese (Simplified), Chinese (Traditional), Korean

English Keyboard Layout

- USA Layout, UK Layout

Timer Settings

Date/Time Settings

- Date Format
 - YYYY MM/DD, MM/DD/YYYY, DD/MM YYYY
- Time Format
 - 12 Hour (AM/PM), 24 Hour
- Current Date/Time Settings
 - Time Zone
 - (UTC-12:00) International Date Line West to (UTC-05:00) Eastern Time (US & Canada) to (UTC+14:00) Christmas Island
 - Daylight Saving Time Settings
 - Off, On
 - Start: Month, Week, Day
 - End: Month, Week, Day
- Auto Reset Time
 - 0 (Auto Reset is disabled.), 1 to 2 to 9 (min.)
- Function After Auto Reset
 - Default Function, Selected Function
- Auto Sleep Time
 - 3 to 240 (min.)

Common Settings

- Switch Paper Feed Method
 - Multi-Purpose Tray
 - Speed Priority, Print Side Priority
 - Drawer 1
 - Speed Priority, Print Side Priority
 - Drawer 2*
 - Speed Priority, Print Side Priority

Settings marked with an asterisk (*) are only available when the optional paper feeder (drawer 2) is attached.

Memory Media Print Settings

Change Default Settings

- Number of Copies
 - 1 to 99
- Paper
 - Multi-Purpose Tray, Drawer 1, Drawer 2*
- N on 1
 - Off, 2 on 1, 4 on 1
- 2-Sided Printing
 - Off, Book Type, Calendar Type
- Print Quality
 - Density
 - 17 Levels
 - Fine Adjust
 - High:17 Levels
 - Medium:17 Levels
 - Low:17 Levels
 - Toner Save
 - Off, On
- Set JPEG/TIFF Details
 - Print Date
 - Off, On
 - Print File Name
 - Off, On
 - Original Type
 - Photo Priority, Text Priority
 - Brightness
 - Five Levels
 - Halftones
 - Gradation, Error Diffusion
 - Grayscale Conversion
 - sRGB, NTSC, Uniform RGB
- Set PDF Details
 - Enlarge/Reduce to Fit Paper Size
 - Off, On
 - Enlarge Print Area
 - Off, On
 - Print Comments
 - Off, Auto
 - Password to Open Document
 - Other
 - Halftones
 - Text:
 - Resolution, Gradation, High Resolution
 - Graphics:
 - Resolution, Gradation, High Resolution
 - Image:
 - Resolution, Gradation, High Resolution
 - Grayscale Conversion
 - sRGB, NTSC, Uniform RGB

Settings marked with an asterisk (*) are only available when the optional paper feeder(drawer 2) is attached.

Printer Settings

Action When Free Paper Size Mismatch

- Multi-Purpose Tray
 - Force Output, Display Error
- Drawer 1
 - Force Output, Display Error
- Drawer 2*
 - Force Output, Display Error

Copies

- 1 to 99

2-Sided Printing

- Off, On

Default Paper

Paper Size Override

- Off, On

Print Quality

- Density
 - 17 Levels
 - Fine Adjust
 - High(17 Levels)
 - Medium(17 Levels)
 - Low(17 Levels)
- Toner Save
 - Off, On
- Resolution
 - 1200 dpi, 600 dpi
- Barcode Adjustment Mode
 - Off, Mode 1, Mode 2, Mode 3

Layout

- Binding Location
 - Long Edge, Short Edge
- Gutter
 - 1.90 to 0.00 to +1.90 (inches) or -50.0 to 0.00 to +50.0 (mm)
- Offset Short Edge/Offset Long Edge
 - 2.00 to 0.00 to +2.00 (inches) or -50.0 to 0.00 to +50.0 (mm)

Auto Error Skip

- Off, On

Timeout

- 5 to 15 to 300 (sec.)

Personality

- Auto, PS, PCL, PDF, XPS

Prioritize Multi-Purpose Tray

- Off, On

UFR II

- Halftones
 - Text
 - Resolution, Color Tone, Gradation, High Resolution
 - Graphics
 - Resolution, Color Tone, Gradation, High Resolution
 - Image
 - Resolution, Color Tone, Gradation, High Resolution

PCL

- Paper Save
 - Off, On
- Orientation
 - Portrait, Landscape
- Font Number
 - 0 to 104
- Point Size
 - 4.00 to 12.00 to 999.75 (point)
- Pitch
 - 0.44 to 10.00 to 99.99 (cpi)
- Form Lines
 - 5 to 60 to 128 (lines)
- Character Code
 - ARABIC8, DESKTOP, GREEK8, HEBREW7, HEBREW8, ISO4, ISO6, ISO11, ISO15, ISO17, ISO21, ISO60, ISO69, ISOCYR, ISOGRK, ISOHEB, ISOLL1, ISOLL2, ISOLL5, ISOLL6, LEGAL, MATH8, MCTEXT, MSPUBL, PC775, PC8, PC850, PC851, PC852, PC862, PC864, PC866, PC8DN, PC8GRK, PC8TX, PC1004, PIFONT, PSMATH, PSTEXT, ROMAN8, VININTL, VNMATH, VNUS, WIN30, WINAR8, WINBAL, WINCYR, WINGRK, WINL1, WINL2, WINL5

Custom Paper

- Off, On
- Unit of Measure
 - Millimeters, Inches
- X dimension
 - 3 to 8 1/2 (inches) or 77 to 216 (mm)
- Y dimension
 - 5 to 14 (inches) or 127 to 356 (mm)
- Append CR to LF
 - Yes, No
- Enlarge A4 Print Width
 - Off, On
- Halftones
 - Text
 - Resolution, Color Tone, Gradation, High Resolution
 - Graphics
 - Resolution, Color Tone, Gradation, High Resolution
 - Image
 - Resolution, Color Tone, Gradation, High Resolution

PS

- Job Timeout
 - 0 to 3600 (sec.)
- Print PS Errors
 - Off, On
- Halftones
 - Text
 - Resolution, Gradation, High Resolution
 - Graphics
 - Resolution, Gradation, High Resolution
 - Image
 - Resolution, Gradation, High Resolution
- Grayscale Conversion
 - sRGB, NTSC, Uniform RGB

PDF

- Enlarge/Reduce to Fit Paper Size
 - Off, On
- Enlarge Print Area
 - Off, On
- N on 1
 - Off, 2 on 1, 4 on 1, 6 on 1, 8 on 1, 9 on 1, 16 on 1
- Print Comments
 - Off, Auto
- Halftones
 - Text
 - Resolution, Gradation, High Resolution
 - Graphics
 - Resolution, Gradation, High Resolution
 - Image
 - Resolution, Gradation, High Resolution
- Grayscale Conversion
 - sRGB, NTSC, Uniform RGB

XPS

- Halftones
 - Text
 - Resolution, Gradation, High Resolution
 - Graphics
 - Resolution, Gradation, High Resolution
 - Image
 - Resolution, Gradation, High Resolution
- Grayscale Conversion
 - sRGB, NTSC, Uniform RGB
- Compressed Image Output
 - Output, Display Error

Settings marked with an asterisk (*) are only available when the optional paper feeder (drawer 2) is attached.

Adjustment/Maintenance

Display Timing for Cartridge Preparation Notification

- Auto
- Custom
 - 1 to 20 to 99 (%)

Printer Density

- Nine Levels

Toner Save

- Off, On

Adjust Print Position

- Multi-Purpose Tray
 - Adjust Vertically (Front Side)
 - 0.20 to 0.00 to +0.20 (") or -5.0 to 0.0 to +5.0 (mm)
 - Adjust Horizontally (Front Side)
 - 0.12 to 0.00 to +0.12 (") or -3.0 to 0.0 to +3.0 (mm)
 - Adjust Vertically (Back Side)
 - 0.20 to 0.00 to +0.20 (") or -5.0 to 0.0 to +5.0 (mm)
 - Adjust Horizontally (Back Side)
 - 0.12 to 0.00 to +0.12 (") or -3.0 to 0.0 to +3.0 (mm)
- Drawer 1
 - Adjust Vertically (Front Side)
 - 0.20 to 0.00 to +0.20 (") or -5.0 to 0.0 to +5.0 (mm)
 - Adjust Horizontally (Front Side)
 - 0.12 to 0.00 to +0.12 (") or -3.0 to 0.0 to +3.0 (mm)
 - Adjust Vertically (Back Side)
 - 0.20 to 0.00 to +0.20 (") or -5.0 to 0.0 to +5.0 (mm)
 - Adjust Horizontally (Back Side)
 - 0.12 to 0.00 to +0.12 (") or -3.0 to 0.0 to +3.0 (mm)
- Drawer 2*
 - Adjust Vertically (Front Side)
 - 0.20 to 0.00 to +0.20 (") or -5.0 to 0.0 to +5.0 (mm)
 - Adjust Horizontally (Front Side)
 - 0.12 to 0.00 to +0.12 (") or -3.0 to 0.0 to +3.0 (mm)
 - Adjust Vertically (Back Side)
 - 0.20 to 0.00 to +0.20 (") or -5.0 to 0.0 to +5.0 (mm)
 - Adjust Horizontally (Back Side)
 - 0.12 to 0.00 to +0.12 (") or -3.0 to 0.0 to +3.0 (mm)

Special Processing

- Special Printing Mode A
 - Off, Mode 1, Mode 2, Mode 3, Mode 4
- Special Printing Mode U
 - Off, On
- Special Printing Mode V
 - Off, Mode 1, Mode 2
- Special Printing Mode B
 - Off, Mode 1, Mode 2, Mode 3
- Special Printing Mode D
 - Off, On

Clean Fixing Assembly

Settings marked with an asterisk (*) are only available when the optional paper feeder (drawer 2) is attached.

Menu Route Map

